

Size and colour chart

Tights – Above Ankle – Child

SIZES

Size	Waist (a)	Hips (b)	Top leg (c)	Knee (d)	Inside leg length to ankle (e)
2	47 – 50cm	47.5 – 51.5cm	26.5 – 31cm	20 – 21.5cm	34cm
4	50 – 53.5cm	51.5 – 57cm	31 – 35cm	21.5 – 23.5cm	40cm
6	53.5 – 57cm	57 – 63cm	35 – 38cm	23.5 – 25.5cm	46cm
8	57 – 60cm	63 – 69cm	38 – 42cm	25.5 – 27.5cm	52cm
10	60 – 64cm	69 – 76cm	42 – 46cm	27.5 – 29.5cm	58cm
12	64 – 68cm	76 – 83cm	46 – 50cm	29.5 – 32.5cm	64cm


COLOURS



Light



Dark




Black


MEASUREMENTS

Measuring Tips:


- All circumferences to be measured to the nearest millimetre.
- Tape should be snug NOT tight.
- Waist measurement is taken over the navel.
- Hip measurement is taken over top of hip bone.
- Knee measurement is over the middle of the patella.
- Leg length is measured to the end of the tights.




FABRIC OPTIONS



Powernet



Shimmer



Hydro

Please note that garments *cannot* be altered or repaired by Second Skin.



Second Skin Pty Ltd
40 O'Malley Street
Osborne Park WA Australia 6017
Email: perth@secondskin.com.au
Phone: +61 8 9201 9455



Second Skin
10/32-34 Gordon House Road
Gospel Oak, LONDON NW5 1LP
Email: london@secondskin.com.au
Phone: +44 203 627 9937





Second Skin

CUSTOMISED COMPRESSION GARMENTS & SPLINTS

Fabric options

All Second Skin garments are made from a range of medical grade stretch fabrics. Several highly durable medical grade fabrics are incorporated in our garment designs, to address the individual needs of each client.

POWERNET FABRICS

Powernet is an open weave fabric which is prescribed for healed skin and for areas where additional support and compression is required. This fabric is particularly durable in work, school or outdoor activities. Powernet is often used in burns scar management and lymphoedema.

Our Powernet fabric now incorporates patented cooling properties, HeiQ Smart Temp, which provides outstanding thermal comfort to clients by keeping them cooler and dryer while wearing their garment.

Powernet fabric is available in light tan, dark tan and black.

SHIMMER FABRICS

Shimmer is a closed weave fabric which provides a softer interface with the skin. Shimmer fabric contours well and is comfortable and effective over joint surfaces and areas of skin fragility such as the elbow, ankle and knee. Shimmer fabric is used for early burns and flap management, external fixators, vascular conditions and certain types of lymphoedema.

Shimmer fabric is available in light tan, dark tan and black.

HYDROPHOBIC FABRICS

Hydrophobic fabric is used as both a lining and a base fabric in compression garments. This fabric wicks moisture away from the surface of the skin to evaporate, protecting the skin surface and ensuring optimal comfort.

Our hydrophobic fabric has an antimicrobial component embedded within the matrix of the fabric. This ensures our products are breathable and highly effective at removing bacteria from the fabric surface, to provide the wearer with all year round comfort. Due to this innovation, our garments are frequently prescribed to assist with the management of repeated skin breakdown and fragility.

Hydrophobic fabric is available in light tan, dark tan and black.

PERTH OFFICE

40 O'Malley Street
OSBORNE PARK
WA 6017

P: +61 8 9201 9455

E: perth@secondskin.com.au

UK OFFICE

Unit 10, Spectrum House
32-34 Gordon House Road
Gospel Oak, LONDON NW5 1LP

P: 0203 6279937

E: london@secondskin.com.au

 Follow us on LinkedIn